







VOLUMEN (l)
VOLUMEN (l)

MAX. OBREMENITEV (kg)
MAX. OBTEREČENJE (kg)

OBREMENITEV TAL (kg/m²)
OBTEREČENJE PODA (kg/m²)

400

400

295

- – Prostor za el. vodnik 3 x 2,5 mm², dolžine cca 1m.
- – Mjesto za el. vodnik 3 x 2,5 mm², dužine cca 1m.
- – Prostor za el. vodnik 1 x 6 mm² za ozemljitev, dolžine cca 1,5m.
- – Mjesto za el. vodnik 1 x 6 mm² za ozemljenje, dužine cca 1,5m.




- Priklop tople in hladne vode 1/2" min 0,2 Mpa, max 0,4 Mpa
- Priključak tople i hladne vode 1/2" min 0,2 Mpa, max 0,4 Mpa



- Prostor za odtok ø 50 mm
- Mjesto za odtok ø 50 mm

PREDLOG VGRADNJE
PRIJEDLOG UGRADNJE



Priporočena prelivna garnitura
Preporuka prelivne garniture

PAL 650

Priporočila za vgradnjo kadi brez obloge
Preporuka za ugradnjo kade bez obloge


Nr. MK 03


Opcija podnožja kadi za vgradnjo
Varianta postolja za kade bez obloge

Nr. MK 05
PKK 501

BELL-E2 170x80

POLOŽAJ STIKAL IN AGREGATOV PRI RAZLIČNIH IZVEDBAH MASAŽNIH SISTEMOV
MJESTO PREKIDAČA I AGREGATA KOT RAZLIČITIH IZVEDBI MASAŽNIH SISTEMA

 - VODNA ČRPALKA - ČRPKA ZA VODU	 - VODNE ŠOBE - VODENE MLAZNICE	 - REGULATOR ZRAKA - REGULATOR ZRAKA	 - ELEKTRONSKA STIKALA - ELEKTRONSKI PREKIDAČI	 - ARMATURA IN TUŠ ROČICA - PIPA I TUŠ
 - ZRAČNI KOMPRESOR - ZRAČNI KOMPRESOR	 - ZRAČNA ŠOBA - ZRAČNA MLAZNICA	 - PNEVMATSKO STIKALO - PNEVMATSKI PREKIDAČ	 - LUČ ALI CHROMOTERAPIJA - SVJETLO ILI CHROMOTERAPIJA	 - PREKLOPNIK ZA MIKROŠOBE - PREKIDAČ ZA MIKROMLAZNICE



- OPCIJA ARMATURA IN TUŠ ROČICA - OPCIJA PIPA I TUŠ